



Asymmetric Configuration



Symmetric Configuration



STANDARD MODELS	STANDARD ARMS							
	XPR-10A		XPR-10		XPR-9D		XPR-9	
BendPak Lift Models	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING
Configuration	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING
Arm Config.	3-Stage Front	3-Stage Front	3-Stage Front	3-Stage Front	3-Stage Front	3-Stage Front	3-Stage Front	3-Stage Front
Type	True Asymmetric	True Asymmetric	Symmetric	Symmetric	Symmetric	Symmetric	Symmetric	Symmetric
Capacity	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds
Front Arm Min (C)	23.4	23.4	25.4	25.4	25.4	25.4	25.4	25.4
Front Arm Max (C)	43.7	43.7	49.4	49.4	49.4	49.4	49.4	49.4
Front Arm Movement	20.3	20.3	24	24	24	24	24	24
Front Arm Distance Apart / Retracted (D)	46	59	46.7	59.7	46.2	59.2	45.9	58.9
Front Arm Distance Apart / Extended (D)	5.4	18.4	-1.3	11.7	-1.8	11.2	-2.1	10.9
Rear Arm Min (E)	40.3	40.3	32.3	32.3	32.3	32.3	32.3	32.3
Rear Arm Max (E)	58	58	52.5	52.5	52.5	52.5	52.5	52.5
Rear Arm Movement	17.7	17.7	20.2	20.2	20.2	20.2	20.2	20.2
Rear Arm Distance Apart / Retracted (F)	23.2	36.2	32.9	45.9	32.4	45.4	32.1	45.1
Rear Arm Distance Apart / Extended (F)	-12.2	0.8	-7.5	5.5	-8	5	-8.3	4.7

LP MODELS	LOW PROFILE ARMS							
	XPR-10A-LP		XPR-10-LP		XPR-9D-LP		XPR-9-LP	
BendPak Lift Models	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING
Configuration	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING	NARROW SETTING	WIDE SETTING
Arm Config.	2-Stage	2-Stage	2-Stage	2-Stage	2-Stage	2-Stage	2-Stage	2-Stage
Type	True Asymmetric	True Asymmetric	Symmetric	Symmetric	Symmetric	Symmetric	Symmetric	Symmetric
Capacity	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds	10,000 Pounds
Front Arm Min (C)	23.3	23.3	28.5	28.5	28.5	28.5	28.5	28.5
Front Arm Max (C)	38.5	38.5	47.5	47.5	47.5	47.5	47.5	47.5
Front Arm Movement	15.2	15.2	19	19	19	19	19	19
Front Arm Distance Apart / Retracted (D)	46.2	59.2	40.5	53.5	40	53	39.7	52.7
Front Arm Distance Apart / Extended (D)	15.8	28.8	2.5	15.5	2	15	1.7	14.7
Rear Arm Min (E)	34.5	34.5	28.5	28.5	28.5	28.5	28.5	28.5
Rear Arm Max (E)	54.5	54.5	47.5	47.5	47.5	47.5	47.5	47.5
Rear Arm Movement	20	20	19	19	19	19	19	19
Rear Arm Distance Apart / Retracted (F)	34.8	47.8	40.5	53.5	40	53	39.7	52.7
Rear Arm Distance Apart / Extended (F)	-5.2	7.8	2.5	15.5	2	15	1.7	14.7